

NGFB-CB4QR2K1166

Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 192 LC/UPC, singlemode, right oriented, putty white

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch/splice block
Product Series	NGFB

General Specifications

Functionality	Patching Splicing
Application	Used in NGF-style frames only
Body Style	Right orientation
Cable Exit Location	Rear, bottom side
Color	Black
Color, front	Black
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	192

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

NGFB-CB4QR2K1166

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

