## 760202572 | 360-iP-1100A-E-GS6-2U-48



SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Angled Patch Panel, 48 port

## Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type RJ45 patch panel

Product Brand SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category 6A

Cable TypeUnshieldedColorCool gray

Intelligence Type iPatch® enabled

Panel Style Angled

Rack Units 2

Total Ports, quantity 48

**Wiring** T568A | T568B

**Dimensions** 

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 266.7 mm | 10.5 in

 Compatible Diameter Over Dielectric, maximum
 1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum 0.762 mm | 0.03 in

**Electrical Specifications** 

**Current Rating at Temperature** 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

COMMSCOPE®

## 760202572 | 360-iP-1100A-E-GS6-2U-48

**Insulation Resistance, minimum** 500 MOhm

Material Specifications

Contact Plating Material Precious metals

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

**Environmental Specifications** 

**Operating Temperature**  $-5 \,^{\circ}\text{C}$  to  $+50 \,^{\circ}\text{C}$  ( $+23 \,^{\circ}\text{F}$  to  $+122 \,^{\circ}\text{F}$ )

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard ACMA | CE | CSA | UL

Packaging and Weights

Included Eight "A" labels | Eight #12-24 mounting screws | Forty-

eight cable ties | Instruction sheet | Panel | Two cable

management bars

Packaging quantity 1

**Weight, net** 1.814 kg | 4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

