

# 760236109 | DM08-24LC-WB-ULL



G2 ULL Multimode OM5 MPO-8 Distribution Module, 24LC to 3x8f MPOs unpinned, internal shutters

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber module  |
| <b>Product Brand</b>         | SYSTIMAX ULL  |
| <b>Product Series</b>        | G2  |

## General Specifications

|                                |                            |
|--------------------------------|----------------------------|
| <b>Functionality</b>           | Breakout                   |
| <b>Color, front</b>            | Lime green                 |
| <b>Color, rear</b>             | Gray                       |
| <b>Interface, front</b>        | LC/UPC                     |
| <b>Interface, rear</b>         | MPO                        |
| <b>Interface Feature, rear</b> | Key up/up   MPO Non-Pinned |
| <b>Polarity</b>                | Method B Enhanced (ULL)    |
| <b>Shuttered</b>               | Yes                        |
| <b>Total Fibers, quantity</b>  | 24                         |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 26.42 mm   1.04 in  |
| <b>Width</b>  | 96.52 mm   3.8 in   |
| <b>Depth</b>  | 117.35 mm   4.62 in |

## Optical Specifications

|                                |                          |
|--------------------------------|--------------------------|
| <b>Fiber Mode</b>              | Multimode                |
| <b>Fiber Type</b>              | OM5, LazrSPEED® wideband |
| <b>Insertion Loss, maximum</b> | 0.35 dB                  |

# 760236109 | DM08-24LC-WB-ULL

---

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D  
**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 0.113 kg | 0.249 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

