

LDX-6513DS-VTM | LDX-6513DS-A1M



2-port sector antenna, 2x 790–960 MHz, 65° HPBW, RET compatible

- Engineered to provide wideband capability to support “Digital Dividend” band applications, future ready
- Same physical size as existing 800/900 MHz antennas for easy site zoning
- Proven core design technology, with over 1,000,000 similar antennas deployed

OBSOLETE

This product was discontinued on: March 30, 2024

General Specifications

Antenna Type	Sector
Band	Single band
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	PVC, UV resistant
Radiator Material	Aluminum
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	0
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	2
RF Connector Quantity, total	2

Remote Electrical Tilt (RET) Information

Model with Factory Installed AISG 2.0 Actuator	LDX-6513DS-A1M
---	----------------

Dimensions

Width	269 mm 10.591 in
Depth	132 mm 5.197 in
Length	1297 mm 51.063 in

LDX-6513DS-VTM | LDX-6513DS-A1M

Net Weight, without mounting kit

9.3 kg | 20.503 lb

Array Layout



Array	Freq (MHz)	Conns
R1	790-960	1-2

Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	790 – 960 MHz
Polarization	±45°

Electrical Specifications

Frequency Band, MHz	790–896	870–960
Gain, dBi	15	15.4
Beamwidth, Horizontal, degrees	66	65
Beamwidth, Vertical, degrees	15.1	14.3
Beam Tilt, degrees	0–15	0–15
USLS (First Lobe), dB	16	15
Front-to-Back Ratio at 180°, dB	32	30
CPR at Boresight, dB	23	23
CPR at Sector, dB	12	10
Isolation, Cross Polarization, dB	30	30
VSWR Return loss, dB	1.4 15.6	1.4 15.6
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153

LDX-6513DS-VTM | LDX-6513DS-A1M

Input Power per Port, maximum, watts 350 350

Mechanical Specifications

Wind Loading @ Velocity, frontal 402.0 N @ 150 km/h (90.4 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral 90.0 N @ 150 km/h (20.2 lbf @ 150 km/h)
Wind Loading @ Velocity, rear 436.0 N @ 150 km/h (98.0 lbf @ 150 km/h)
Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

Width, packed 376 mm | 14.803 in
Depth, packed 267 mm | 10.512 in
Length, packed 1610 mm | 63.386 in
Weight, gross 20.3 kg | 44.754 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

600899A-2 – Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

600899A-2



Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 114.3 mm | 4.5 in

Compatible Diameter, minimum 61 mm | 2.402 in

Weight, net 3.9 kg | 8.598 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Weight, gross 4.2 kg | 9.259 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

600899A-2

