

Category 5e F/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length, reel

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America North America
Portfolio	CommScope®
Product Type	Twisted pair cable


General Specifications

Product Number	CS24R
ANSI/TIA Category	5e
Cable Component Type	Horizontal
Cable Type	F/UTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Drain Wire Type	Solid
Jacket Color	Blue
Note	All electrical transmission tests include swept frequency measurements
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-3-1 ISO/IEC 11801 Class D

Dimensions

Cable Length	304.8 m 1000 ft
Diameter Over Jacket, nominal	6.147 mm 0.242 in
Jacket Thickness	0.508 mm 0.02 in
Conductor Gauge, singles	24 AWG
Drain Wire Gauge	26 AWG

Cross Section Drawing



Electrical Specifications

Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m 2.859 ohms/100 ft
Delay Skew, maximum	15 ns
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	100 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Electrical Cable Performance

CS	CommScope	NEXT	Near End Crosstalk (dB/100m)
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	PSNEXT	Power Sum Near End Crosstalk (db/100m)
TYP	Typical Electrical Performance	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
IL	Insertion Loss (dB/100m)	RL	Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
TCL	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2	1.9	65.3	83.1	63.3	81.2	62.3	80.8	60.3	78.9	63.8	84.4	60.8	82.4	20	33
4	4.1	3.7	56.3	73.4	52.2	69.8	53.3	71.3	49.2	67.6	51.8	73.3	48.8	71.4	23	30.6
8	5.8	5.2	51.8	69	46	63.9	48.8	67	43	61.8	45.7	67.4	42.7	65.5	24.5	31.5
10	6.5	5.8	50.3	67.2	43.8	61.4	47.3	65.1	40.8	59.3	43.8	65.4	40.8	63.5	25	32.4
16	8.2	7.4	47.2	64.1	39	56.8	44.2	62	36	54.7	39.7	61.3	36.7	59.4	25	31.8
20	9.3	8.2	45.8	62.6	36.5	54.4	42.8	60.5	33.5	52.2	37.8	59.4	34.8	57.4	25	33
25	10.4	9.2	44.3	60.9	33.9	51.6	41.3	58.8	30.9	49.6	35.8	57.6	32.8	55.5	24.3	33.1
31.25	11.7	10.3	42.9	59.6	31.2	49.2	39.9	57.4	28.2	47.1	33.9	55.6	30.9	53.5	23.6	33.4
62.5	17	14.7	38.4	54.4	21.4	39.8	35.4	52.4	18.4	37.7	27.9	49.5	24.9	47.4	21.5	32.9
100	22	18.6	35.3	51	13.3	32.4	32.3	48.9	10.3	30.2	23.8	45.5	20.8	43.3	20.1	29.9
155		23.4		46.9		23.5		45.1		21.7		41.3		39.3		28
200		26.7		45.1		18.4		43.2		16.5		39.1		37		26
250		29.9		44.8		14.9		42.7		12.8		37.1		35.1		25.1
300		32.9		43		10.1		40.9		8		35.6		33.4		25
350		35.7		41.6		5.9		39.7		3.9		34.1		31.8		25.6

Material Specifications

Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	Polyolefin
Jacket Material	PVC
Shield (Tape) Material	Aluminum/Polyester

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

884020404/10 | CS24R BLU C5E 4/24 F/UTP RL 1KFT

Environmental Space Non-plenum
Flame Test Method CMR | NEC Article 800 | UL 1666 | UL 444

Packaging and Weights

Cable weight 40.18 kg/km | 27 lb/kft
Packaging Type Reel

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system