## 760213801 | D-060-CA-RB-F12NS/8W/99A



Fiber OSP cable, Steel Armored, Arid-Core, Dry Central Tube Ribbon, 60 fiber, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

\*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

**Product Type** Fiber OSP cable

**Product Series** D-CA

**Government Requirements**Build America Buy America (BABA) compliant\*

General Specifications

Armor Type Corrugated steel

Cable Type Ribbon central tube

Construction TypeArmoredSubunit TypeGel-free

Fibers per Ribbon, quantity 12

Jacket Color Black
Jacket Marking Feet

**Location of Manufacturing**Carrollton, Georgia

Total Fiber Count 60


Dimensions

Buffer Tube/Subunit Diameter7.9 mm | 0.311 inDiameter Over Jacket15.5 mm | 0.61 in

Representative Image



# 760213801 | D-060-CA-RB-F12NS/8W/99A



### Mechanical Specifications

Minimum Bend Radius, loaded 309.9 mm | 12.201 in

Minimum Bend Radius, unloaded 154.9 mm | 6.098 in

Tensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbf

**Compression** 22 N/mm | 125.623 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 4.4 N-m | 38.943 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

**Fiber Type** G.652.D and G.657.A1 | G.652.D and G.657.A1

### **Environmental Specifications**



# 760213801 | D-060-CA-RB-F12NS/8W/99A

Installation temperature $-30 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (-22 °F to } +140 \,^{\circ}\text{F)}$ Operating Temperature $-40 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (-40 °F to } +158 \,^{\circ}\text{F)}$ 

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20

**Environmental Space** Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 213 kg/km | 143.129 lb/kft

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

### Included Products

CS-8W-RB-OUTDOOR - TeraSPEED® Singlemode Fiber Rollable Ribbon

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## CS-8W-RB-OUTDOOR

# TeraSPEED®

### TeraSPEED® Singlemode Fiber Rollable Ribbon

 $0.5 \, \mu m$ 

#### Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance**  $\pm 0.7 \, \mu m$ 0.7 % Cladding Non-Circularity, maximum **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm

**Proof Test** 689.476 N/mm<sup>2</sup> | 100000 psi

**Dimensions** 

Core/Clad Offset, maximum

**Fiber Curl, minimum** 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 1 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 1 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

**COMMSCOPE®** 

# CS-8W-RB-OUTDOOR

### **Optical Specifications**

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.25 dB/km @ 1,550 nm | 0.35 dB/km @ 1,310 nm

**Backscatter Coefficient** -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

**Mode Field Diameter**  $10.4 \, \mu \text{m} \ @ \ 1,550 \, \text{nm} \ | \ 9.2 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,000 \, \text{m}$ 

1,385 nm

Mode Field Diameter Tolerance  $\pm 0.4 \, \mu \text{m}$  @ 1310 nm |  $\pm 0.5 \, \mu \text{m}$  @ 1550 nm |  $\pm 0.6 \, \mu \text{m}$ 

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sqrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

### **Environmental Specifications**

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

### \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

