


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	09-10-08	MO	MO
B		ECN 8000018219 REBRANDING	21012017	RCR	SC

SC CONN. LEFT label		SC CONN. RIGHT label
A	↔	B
B	↔	A



NOTES:

- 1 CONNECTOR ATTENUATION TYPICAL ≤ 0.15 dB, MEASURED AGAINST REF. CONN. AT 850nm
EXTRA CABLE ATTENUATION 0,0035 dB/m
- 2 RETURN LOSS ≥ 35 dB, MEASURED AGAINST REF. CONN. AT 850nm
- 3 TOLERANCE OF THE LENGTH ACC. TO 118-19200
- 4 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm
- 5 CABLE LABEL INFORMATION:
 - BARCODE
 - PART NUMBER
 - UNIQUE SERIAL NUMBER
 - CABLE LENGTH
 - ORDER NUMBER
- 6 100% INSPECTION OF ALL ENDFACES
- 7 PACKAGING IN A BAG AND BOX
- 8 INFORMATION ON PACKAGING LABEL:
 - BARCODE
 - PART NUMBER
 - DESCRIPTION
 - FACTORY ORDER NUMBER
 - PRODUCTION DATE
- 9 TEST RESULT SHEET PACKED WITH EACH INDIVIDUAL ASSEMBLY

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter) 3
X-2055108-Y	XY.0

Qty	Description	Item
6	FOAC DAT-85 LABEL	5
4	FOKIT IMPROVED SC MM SIMPLEX	4
4	FOAC SC DUPLEX CLIP, BLACK	3
4	BOOT BEND LIMITING, BLUE	2
L	FOCAB OM3 1.8TZ 50/125 LSZH, AQUA	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.A.H. Oppers 09OCT2008	COMMSCOPE, INC.	
DIMENSIONS: mm		CHK T. v d Meulen 09OCT2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. v Woesik 09OCT2008	NAME MPOptimate	
0 PLC ± -		PRODUCT SPEC	FOMM OM3 LEAD 1,8MZ SC/PC - SC/PC	
1 PLC ± -		APPLICATION SPEC	DUPLEX XG	
2 PLC ± -		WEIGHT	SIZE A2	DRAWING NO C=2055108
3 PLC ± -		FINISH	RESTRICTED TO	
4 PLC ± -			SCALE 1:1	SHEET 1 of 1
ANGLES ± -			REV B	
MATERIAL		CUSTOMER DRAWING		

2055108