760213439 | D-012-CN-RB-F12NS/8W/99A



Fiber OSP Cable, Non-Armored, All-Dielectric, Arid-Core, Dry Central Tube Ribbon, 12 fibers, Singlemode G.652.D and G.657.A1, Gel-free, Feet jacket marking, Black jacket color

*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber OSP cable

Product Series D-CN

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

 Cable Type
 Ribbon central tube

Construction Type Non-armored

Subunit Type Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet

Location of ManufacturingCarrollton, Georgia

Total Fiber Count 12

Dimensions


Buffer Tube/Subunit Diameter 6 mm | 0.236 in

Diameter Over Jacket 12.6 mm | 0.496 in

Representative Image



760213439 | D-012-CN-RB-F12NS/8W/99A



Mechanical Specifications

Minimum Bend Radius, loaded 251.5 mm | 9.902 in

Minimum Bend Radius, unloaded 127 mm | 5 in

Tensile Load, long term, maximum 800 N | 179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 22 N/mm | 125.623 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.4 N-m | 38.943 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE°

760213439 | D-012-CN-RB-F12NS/8W/99A

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 130 kg/km | 87.356 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8W-RB-OUTDOOR - TeraSPEED® Singlemode Fiber Rollable Ribbon

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8W-RB-OUTDOOR

TeraSPEED®

TeraSPEED® Singlemode Fiber Rollable Ribbon

 $0.5 \, \mu m$

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** $\pm 0.7 \, \mu m$ 0.7 % Cladding Non-Circularity, maximum **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Core/Clad Offset, maximum

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 1 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 1 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

COMMSCOPE®

CS-8W-RB-OUTDOOR

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.25 dB/km @ 1,550 nm | 0.35 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

Mode Field Diameter $10.4 \, \mu \text{m} \ @ \ 1,550 \, \text{nm} \ | \ 9.2 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,000 \, \text{m}$

1,385 nm

Mode Field Diameter Tolerance $\pm 0.4 \, \mu \text{m}$ @ 1310 nm | $\pm 0.5 \, \mu \text{m}$ @ 1550 nm | $\pm 0.6 \, \mu \text{m}$

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sqrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

