



Fiber indoor/outdoor drop cable, LSZH, Gel-filled Central Tube, CST, 24 fiber, Multimode OM4, Meters jacket marking, Black jacket color

Product Classification

| | |
|------------------------------|------------------------------|
| Regional Availability | Asia Australia/New Zealand |
| Portfolio | CommScope® |
| Product Type | Fiber drop cable |
| Product Series | O-DA |

General Specifications

| | |
|-------------------------------------|--------------------|
| Cable Type | Central loose tube |
| Construction Type | Armored |
| Subunit Type | Gel-filled |
| Jacket Color | Black |
| Jacket Marking | Meters |
| Fibers per Subunit, quantity | 24 |
| Total Fiber Count | 24 |

Dimensions

| | |
|-------------------------------------|-------------------|
| Buffer Tube/Subunit Diameter | 2.8 mm 0.11 in |
| Diameter Over Jacket | 8.7 mm 0.343 in |

Mechanical Specifications

| | |
|--|------------------------|
| Minimum Bend Radius, loaded | 174 mm 6.85 in |
| Minimum Bend Radius, unloaded | 87 mm 3.425 in |
| Tensile Load, long term, maximum | 800 N 179.847 lbf |
| Tensile Load, short term, maximum | 1500 N 337.214 lbf |
| Compression | 15 N/mm 85.652 lb/in |
| Compression Test Method | IEC 60794-1-2 E3 |

760249727 | C-024-CA-5X-M24BK/28G/093

| | |
|---------------------------|---------------------------------------|
| Strain | See long and short term tensile loads |
| Strain Test Method | IEC 60794-1-2-E1 |

Optical Specifications

| | |
|-------------------|-----|
| Fiber Type | OM4 |
|-------------------|-----|

Optical Specifications, Wavelength Specific

| | |
|-----------------------------|---|
| Attenuation, maximum | 1.00 dB/km @ 1,300 nm 3.00 dB/km @ 850 nm |
|-----------------------------|---|

Environmental Specifications

| | |
|--------------------------------------|--------------------------------------|
| Installation temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Environmental Space | Buried Ducted Indoor/Outdoor |
| Flame Test Method | IEC 60332-1 IEC 60332-3-24 |
| Water Penetration | 24 h |
| Water Penetration Test Method | IEC 60794-1 F5B |

Environmental Test Specifications

| | |
|--------------------------------------|--------------------------------------|
| Temperature Cycle | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | IEC 60794-1-2 F1 |

Packaging and Weights

| | |
|---------------------|--------------------------|
| Cable weight | 95 kg/km 63.837 lb/kft |
|---------------------|--------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

760249727 | C-024-CA-5X-M24BK/28G/093

Operating Temperature Specification applicable to non-terminated bulk fiber cable