



KJ-Series Modular Jack, RJ45, Cat5e Unshielded, Blue

OBSOLETE

This product was discontinued on: September 30, 2024

Replaced By:

2291217-BL
KJ510-BL

KJ-Series Modular Jack, RJ45, Cat5e Unshielded, Blue

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Modular jack

Product Series

KJ Series

General Specifications

ANSI/TIA Category

5e

Cable Type

Unshielded

Color

Blue

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting

Hubbell® faceplates | Leviton® faceplates | Panduit® faceplates

Outlet Type

Keystone

Termination Tool

110 Punchdown tool | SL Termination tool

Termination Type

IDC

Transmission Standards

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class D

Wiring

T568A | T568B

Dimensions

2291217-6 | KJ510-BL

| | |
|---|-----------------------------------|
| Panel Cutout, recommended | 14.79 x 19.31 mm (0.58 x 0.76 in) |
| Panel Thickness, recommended | 1.6 mm 0.063 in |
| Height | 16.13 mm 0.635 in |
| Width | 16.48 mm 0.649 in |
| Depth | 30.48 mm 1.2 in |
| Compatible Insulated Conductor Diameter, maximum | 1.27 mm 0.05 in |
| Contact Plating Thickness | 1.27 µm |
| Compatible Conductor Gauge, solid | 24–22 AWG |
| Compatible Conductor Gauge, stranded | 26–24 AWG |

Electrical Specifications

| | |
|------------------------|--|
| Remote Powering | Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002 |
| PoE Durability | Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles |

Material Specifications

| | |
|---------------------------------|------------------|
| Contact Base Material | Beryllium copper |
| Contact Plating Material | Gold |
| Material Type | Polycarbonate |

Mechanical Specifications

| | |
|-----------------------------------|--------------------------------|
| Plug to Jack Mating Cycles | Complies to IEC 60603-7 series |
|-----------------------------------|--------------------------------|

Environmental Specifications

| | |
|----------------------------|-----------|
| Flammability Rating | UL 94 V-0 |
|----------------------------|-----------|

Packaging and Weights

| | |
|---------------------------|-----|
| Packaging quantity | 1 |
| Packaging Type | Bag |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |

2291217-6 | KJ510-BL

ROHS Compliant
UK-ROHS Compliant

