FHD-H01B



Fiber Optic Drop Cable Assembly, hardened full-size to stub, locatable flat

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Hardened drop cables incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117-58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Europe | Latin America | North

America

Product Type Fiber drop cable assembly

Product Series FHD

Government RequirementsBuild America Buy America (BABA) compliant*

Ordering Note Drops are automatically coiled 0 to 1,000 ft (305 m), unless spool option "L" or "R" is

specified for this range of length | Drops are automatically spooled at 1,001 ft (306

m) with connector B deploying first from spool

General Specifications

Cable Type Locatable - Flat

Connector A, quantity 1

Color, boot A Black
Color, connector A Black

Interface, Connector A Hardened full-size SC/APC

Interface, Connector B Unterminated

Jacket Color Black

Location of ManufacturingCatawba, North Carolina

Total Fibers, quantity

Transmission Standards IEC 61753-1 | IEC 61754-4 | IEC 61755

Dimensions

COMMSCOPE®


FHD-H01B

Cable Assembly Length Range (m) 1 - 750

Cable Assembly Length Range (ft) 50 - 2000


Cable Outer Diameter 4.3 x 9.9 mm (0.17 x 0.39 in)

Ordering Tree



Cable Type K not available with LC & SC Options
Cable Length shown as an example, additional cable lengths available upon request up to 2,000 ft. (600 m).
Special Request Feature not available with cable types K.
Drops are automatically colled 0 to 1,000 ft. unless "L" or "R" is specified for this range of length.
Drops are automatically spooled at 1,001 ft. with Connector B deploying first from spool. Add "L" to lengths over 1,001 ft. if Connector A needs to deploy first. **** Includes pulling sock - 25 lbs. of pulling force

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded 86.36 mm | 3.4 in Minimum Bend Radius, unloaded 81.28 mm | 3.2 in

Page 2 of 3



FHD-H01B

Tensile Load, long term, maximum 400.34 N | 90 lbf

Tensile Load, short term, maximum 1,334.466 N | 300 lbf

Cable Crush Resistance, maximum 22 N/mm | 125.623 lb/in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A1/A2

Insertion Loss, maximum, connector A 0.4 dB

Return Loss, minimum, connector A 65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Outdoor, buried

Qualification Standards NEMA type 6, 10 ft waterhead | Telcordia GR-20 | Telcordia GR-3120

Packaging and Weights

Cable weight 36 kg/km | 24.191 lb/kft

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

