

SHK-19-3-PV2



Hanger Kit for triple stack for 19.6 to 20.1mm cable; includes ten sets of hardware, angle adapters for

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	3
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Length	180.1 mm 7.091 in
Compatible Cable Diameter Range	19.6–20.1 mm
Compatible Diameter, maximum	20.1 mm 0.791 in
Compatible Diameter, minimum	19.6 mm 0.772 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel 304
----------------------	--

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

SHK-19-3-PV2

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Included	Angle adapter Hardware
Packaging quantity	10
Weight, gross	2.8 kg 6.173 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power