

# SHK-24-1-PV2

---



Hanger Kit for single stack for 23.6 to 24.1mm cable; includes ten sets of hardware, angle adapters

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	1
<b>Length</b>	103.9 mm   4.091 in
<b>Compatible Cable Diameter Range</b>	23.6–24.1 mm
<b>Compatible Diameter, maximum</b>	24.1 mm   0.949 in
<b>Compatible Diameter, minimum</b>	23.6 mm   0.929 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel 304
----------------------	--

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

# SHK-24-1-PV2

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Included</b>	Angle adapter   Hardware
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	2.8 kg   6.173 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power