


5-1427070-7 | CS30Z3 RED C6 4/24 U/UTP RIB 305M ANATEL



Category 6 U/UTP Cable, 24AWG, low smoke zero halogen, red jacket, 4 pair count, 305 m length Reel in box

Product Classification

Regional Availability	Latin America
Portfolio	NETCONNECT®
Product Type	Twisted pair cable


General Specifications

Product Number	CS30Z3
ANSI/TIA Category	6
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Red
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ABNT/NBR 14703 ANSI/TIA-568.2-D Anatel

Dimensions

Cable Length	304.8 m 1000 ft
Diameter Over Insulated Conductor	0.978 mm 0.038 in
Diameter Over Jacket, nominal	5.588 mm 0.22 in
Conductor Gauge, singles	24 AWG

Cross Section Drawing



Electrical Specifications

Characteristic Impedance	100 ohm
Characteristic Impedance Tolerance	±15 ohm
Nominal Velocity of Propagation (NVP)	68 %
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Zero Halogen (LSZH)
Separator Material	Polyolefin

Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Acid Gas Test Method	IEC 60754-2
Environmental Space	Low Smoke Zero Halogen (LSZH)
Flame Test Method	ABNT/NBR 14705 IEC 60332-1 IEC 60332-3-22

5-1427070-7 | CS30Z3 RED C6 4/24 U/UTP RIB 305M ANATEL

Smoke Test Method IEC 61034-2

Packaging and Weights

Packaging Type Reel in box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

