


SP-23200NNNNXBBB | PLC 2X32 900UM NO CONN



Wideband PLC Splitter, singlemode, 2x32, symmetrical split ratio, 0.900 mm cable, no connectors

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

Product Type

Bare splitter

General Specifications

Device Type

Component, rectangular

Functionality

Splitting

Technology Type

Planar lightwave circuit (PLC)

Distribution Type

2 x 32 splitter

Interface, Input

Stub tail

Interface, Output

Stub tail

Split Ratio

Symmetrical

Splitter, quantity

1

Dimensions

Height

9 mm | 0.354 in

Width

12 mm | 0.472 in

Length

100 mm | 3.937 in

Pigtail Length, Input

2.5 m | 8.202 ft

Pigtail Length, Output

2.5 m | 8.202 ft

Pigtail Diameter, Input

0.25 mm | 0.01 in

Pigtail Diameter, Output

0.25 mm | 0.01 in

Optical Specifications

Fiber Type

G.657.A2

Directivity, minimum

55 dB

SP-23200NNNNXBBB | PLC 2X32 900UM NO CONN

Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2.4 dB
Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	17.7 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

Packaging and Weights

Packaging quantity	1
---------------------------	---