

SP-26400NNNNXBBB | PLC 2X64 900UM NO CONN



Wideband PLC Splitter, singlemode, 2x64, symmetrical split ratio, 0.900 mm cable, no connectors

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Bare splitter

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	2 x 64 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	6 mm 0.236 in
Width	40 mm 1.575 in
Length	120 mm 4.724 in
Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.25 mm 0.01 in
Pigtail Diameter, Output	0.25 mm 0.01 in

Optical Specifications

Fiber Type	G.657.A2
Directivity, minimum	55 dB

SP-26400NNNNXBBB | PLC 2X64 900UM NO CONN

Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2.9 dB
Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	21.3 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

Packaging and Weights

Packaging quantity	1
---------------------------	---