

Fiber indoor/outdoor cable LazrSPEED® Indoor/Outdoor Plenum Distribution, 2 fiber single-unit, Multimode OM4, Gel-free, Feet jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series P-OD

General Specifications

 Cable Type
 Distribution

 Construction Type
 Non-armored


Jacket ColorBlackJacket MarkingFeetTotal Fiber Count2

Dimensions

Diameter Over Jacket 4.2 mm | 0.165 in

Representative Image





42 mm | 1.654 in

Mechanical Specifications

Minimum Bend Radius, unloaded

Minimum Bend Radius, loaded 64 mm | 2.52 in

Tensile Load, long term, maximum 300 N | 67.443 lbf

Tensile Load, short term, maximum 1001 N | 225.034 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 100 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE®

Operating Temperature -25 °C to +70 °C (-13 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-20 (water penetration) | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)
Flame Test Method NFPA 130 | NFPA 262

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze Test Method IEC 60794-1 F15

Heat Age $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -40 °C to +70 °C (-40 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 16 kg/km | 10.752 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5K-TB – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

LazrSPEED® 550

Product Classification

Portfolio CommScope®
Product Type Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)** $254 \, \mu m$ **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

Proof Test 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900 μm Tight Buffer Diameter Tolerance $\pm 40 \ \mu m$

Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

 $1.5 \, \mu m$

Coating Strip Force, maximum 8.9 N | 2.001 lbf

COMMSCOPE®

CS-5K-TB

Coating Strip Force, minimum 1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

Zero Dispersion Slope, maximum 0.105 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1316 nmZero Dispersion Wavelength, minimum1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,110 m @ 850 nm | 600 m @ 1,300 nm

10 Gbps Ethernet Distance 550 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 4,700 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 3,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

Differential Mode Delay 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

Index of Refraction 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM4) | IEC 60793-2-10, A1 (OM4)

Environmental Specifications

Heat Aging, maximum 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

COMMSCOPE®

CS-5K-TB

Temperature Dependence, maximum

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity