# 64623447-96MLT | 0-096-LD-8M-M12BL/15G/PE/PA



#### 96 Core OS2 Outdoor Mini Loose Tube - Double Jacket

### **Product Classification**

Regional Availability Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-LN

## General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

**Subunit Type** Gel-filled

**Jacket Color** Blue

Jacket Marking Meters

Subunit, quantity 8

Fibers per Subunit, quantity 12

Total Fiber Count 96


#### **Dimensions**

Buffer Tube/Subunit Diameter1.55 mm0.061 inDiameter Over Jacket7.4 mm0.291 in

## Representative Image



# 64623447-96MLT | 0-096-LD-8M-M12BL/15G/PE/PA



### Material Specifications

Jacket Material Nylon | PE

Mechanical Specifications

Minimum Bend Radius, loaded220 mm | 8.661 inMinimum Bend Radius, unloaded110 mm | 4.331 inTensile Load, short term, maximum2000 N | 449.618 lbf

Tensile Load, snort term, maximum 2000 N | 449.618 lbf

**Compression** 20 N/mm | 114.203 lb/in

**Compression Test Method** IEC 60794-1-21 E3

Flex 25 cycles

 Impact
 1 N-m | 8.851 in lb

 Impact Test Method
 IEC 60794-1-21 E4

**Strain** See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

**Optical Specifications** 

**Fiber Type** G.652.D

Optical Specifications, Wavelength Specific



# 64623447-96MLT | 0-096-LD-8M-M12BL/15G/PE/PA

**Attenuation, maximum** 0.21 dB/km @ 1,550 nm | 0.35 dB/km @ 1,310 nm

### **Environmental Specifications**

Installation temperature0 °C to +50 °C (+32 °F to +122 °F)Operating Temperature0 °C to +50 °C (+32 °F to +122 °F)Storage Temperature-20 °C to +70 °C (-4 °F to +158 °F)Environmental SpaceBuried | Underground (duct)

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** IEC 60794-1 F5C

### **Environmental Test Specifications**

Temperature Cycle -10 °C to +60 °C (+14 °F to +140 °F)

**Temperature Cycle Test Method** IEC 60794-1-22 F1

Packaging and Weights

**Cable weight** 49 kg/km | 32.926 lb/kft

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

