# UGGQPQXTF

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 24-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 3

Color, boot A Gray

Color, connector A Green

Connector B, quantity 3

Color, boot B Gray

Color, connector B Aqua

**Construction Type** Stranded

**Furcation Color** Yellow

Interface, Connector A MPO-08/APC Female

Interface, Connector B MPO-08/APC Male

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 24

Dimensions

Breakout Length 22 in


**COMMSCOPE®** 

# UGGQPQXTF

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$ 

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



# UGGQPQXTF

#### Included Products

760245564 – Fiber indoor cable, Plenum MPO Trunk, 24 fiber multi-unit with 8 fiber subunits, Singlemode G. P-024-MP-8G1-F08YL/20T 657.A2/B2, Feet jacket marking, Yellow jacket color

860659022 – MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm 860659028 – MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm



# 760245564 | P-024-MP-8G1-F08YL/20T



Fiber indoor cable, Plenum MPO Trunk, 24 fiber multi-unit with 8 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber indoor cable

**Product Series** P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Filler, quantity 1

Jacket Color Yellow

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 8

Total Fiber Count 24

Dimensions


**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in

**Diameter Over Jacket** 7.7 mm | 0.303 in

Representative Image



# 760245564 | P-024-MP-8G1-F08YL/20T



### Mechanical Specifications

Minimum Bend Radius, loaded 116 mm | 4.567 in

Minimum Bend Radius, unloaded 77 mm | 3.031 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 320 m | 1,049.869 ft

Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

### **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Operating Temperature  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 5 of 10



# 760245564 | P-024-MP-8G1-F08YL/20T

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $0 \degree \text{C to } +70 \degree \text{C (} +32 \degree \text{F to } +158 \degree \text{F)}$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 64 kg/km | 43.006 lb/kft

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable





#### MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

**COMMSCOPE®** 

#### **Packaging quantity**

1

### Regulatory Compliance/Certifications

Agency	Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





#### MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Total Fiber Count 8

Dimensions

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

**Fiber Mode** Singlemode Fiber Type G.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

COMMSCOPE®

#### **Packaging quantity**

1

### Regulatory Compliance/Certifications

Compliant

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant



**UK-ROHS**