## UJGRXUC8U

**Base Product** 



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 64-Fiber, Dual Rated (OFNR/LSZH)

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America	
Portfolio	CommScope®	
Product Type	Fiber trunk cable assembly	
Product Brand	Propel   SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration	

### General Specifications

Connector A, quantity	4
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	0
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-16/APC Male
Interface, Connector B	Unterminated
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	16
Total Fibers, quantity	64
Dimensions	
Breakout Length	22 in
Cable Assembly Length Range (m)	3 - 305

Page 1 of 8




## UJGRXUC8U

Cable Assembly Length Range (ft)

10 – 999

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb @ 90 °	
Optical Specifications		
Fiber Mode	Singlemode	
Fiber Type	G.657.A2, TeraSPEED®	

### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F	
Environmental Space	Dual Rated LSZH/Riser   Indoor	

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 8



## UJGRXUC8U

Included Products		
760251076 N-064-MP-8G1-F16YL/30T/B2	_	Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 64 fiber with 16- fiber, 3.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating
860661398	-	Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable

Page 3 of 8



# 760251076 | N-064-MP-8G1-F16YL/30T/B2



Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 64 fiber with 16-fiber, 3.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

#### Product Classification


Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	N-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Feet
Subunit, quantity	4
Fibers per Subunit, quantity	16
Total Fiber Count	64
Dimensions	
Buffer Tube/Subunit Diameter	3 mm   0.118 in
Diameter Over Jacket	10.6 mm   0.417 in

#### Representative Image

Page 4 of 8



# 760251076 | N-064-MP-8G1-F16YL/30T/B2



#### Mechanical Specifications

Minimum Bend Radius, loaded	159 mm   6.26 in
Minimum Bend Radius, unloaded	106 mm   4.173 in
Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	1335 N   300.12 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	2.94 N-m   26.021 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	398 m   1,305.774 ft

#### **Optical Specifications**

Fiber Type

G.657.A2/B2

#### **Environmental Specifications**

Installation temperature0 °C to +50 °C (+32 °F to +122 °F)Operating Temperature0 °C to +60 °C (+32 °F to +140 °F)

Page 5 of 8



# 760251076 | N-064-MP-8G1-F16YL/30T/B2

Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)	
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409	
EN50575 CPR Cable EuroClass Fire Performance	B2ca	
EN50575 CPR Cable EuroClass Smoke Rating	s1a	
EN50575 CPR Cable EuroClass Droplets Rating	d2	
EN50575 CPR Cable EuroClass Acidity Rating	al	
Environmental Space	Low Smoke Zero Halogen (LSZH)	
Flame Test Method	IEC 60754-2   IEC 61034-2	

#### Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1
Packaging and Weights	
Cable weight	103 kg/km   69.213 lb/kft

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 6 of 8



## 860661398



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Portfolio	CommScope®	
Product Type	Fiber connector	

#### General Specifications

Color	Green
Color, boot	Black
Ferrule Geometry	Angled
Interface	MPO/APC Male
Interface Feature	Pinned

#### Dimensions

Compatible Cable Diameter	3 mm	0.118 in
---------------------------	------	----------

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.3 dB
Return Loss, minimum	65 dB

### Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 7 of 8



## 860661398

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant



Page 8 of 8

