NG4-VSMRF28



NG4access® Module VAM, Splitter, 1x8, symmetrical split, singlemode, LC /APC, front, right, 2 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Portfolio	CommScope®
Product Type	Splitter module
Product Brand	NG4access®
Product Series	FACT NG4
Government Requirements	Build America Buy America (BABA) compliant*
General Specifications	
Device Type	Plug-and-play module
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Access	Front
Application	For use with NG4 access frames
Distribution Type	1 x 8 splitter (2)
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Location of Manufacturing	Waived per BABA waiver for BEAD Program
Split Ratio	Symmetrical
Splitter, quantity	2

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 1, 2024



NG4-VSMRF28

Tray Orientation	Right orientation
Dimensions	
Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in
Optical Specifications	
Directivity, minimum	55 dB
Performance Grade	Grade O (PLC, low loss)
Polarization Dependent Loss, maximum	0.2 dB
Uniformity, maximum	1.4 dB
Wavelength Range	1260-1625 nm
Insertion Loss, Splitter, maximum	10.8 dB
Return Loss, Connector, minimum	55 dB

Packaging and Weights

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 1, 2024

1

COMMSCOPE®