



Fiber indoor/outdoor cable, LSZH Riser Distribution, 16 fiber single-unit, Multimode OM4 bend insensitive, Meters jacket marking, Aqua jacket color

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-DS

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Jacket Color</b>	Aqua
<b>Jacket Marking</b>	Meters
<b>Strength Members</b>	E-glass yarns
<b>Total Fiber Count</b>	16

## Dimensions

<b>Diameter Over Jacket</b>	7.8 mm   0.307 in
-----------------------------	-------------------

## Material Specifications

<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Inner Jacket Material</b>	Low Smoke Zero Halogen (LSZH)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	756 mm   29.764 in
<b>Minimum Bend Radius, unloaded</b>	78 mm   3.071 in
<b>Tensile Load, short term, maximum</b>	1100 N   247.29 lbf
<b>Compression</b>	5 N/mm   28.551 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Impact</b>	1 N-m   8.851 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain Test Method</b>	IEC 60794-1-21 E1

# 760256277 | C-016-DS-5X-MSUAQ

---

**Twist** 10 cycles  
**Twist Test Method** IEC 60794-1-21 E7

## Optical Specifications

**Fiber Type** OM4, bend insensitive

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

## Environmental Specifications

**Installation temperature** 0 °C to +50 °C (+32 °F to +122 °F)  
**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)  
**Storage Temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Environmental Space** Low Smoke Zero Halogen (LSZH)  
**Flame Test Method** IEC 60332-3-24  
**Water Penetration Test Method** IEC 60794-1 F5C

## Environmental Test Specifications

**Temperature Cycle Test Method** IEC 60794-1-22 F1

## Packaging and Weights

**Cable weight** 52 kg/km | 34.942 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable