NG4-CMDKORJ



NG4access® Cabled Module, singlemode LC/UPC to stub, 216 fiber, rollable ribbon, indoor/outdoor

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber cabled module

Product Brand NG4access®
Product Series LSX | NG4

Ordering Note For fiber modules with custom cable lengths, please contact your local CommScope

representative

General Specifications

Configuration Type NG4 Module to Stub tail

Adapters, quantity, front 108

Body Style Straight orientation

Cable Color Black

Cable TypeIndoor/outdoor - Rollable Ribbon

Color, housingBlackInterface, frontLC/UPCInterface, rearStub tail

Polarity Pairs, straight

Total Fibers, quantity 216

Total Ports, quantity, front 216

Dimensions

Height 13.3 mm | 0.524 in


COMMSCOPE®

NG4-CMDKORJ

Width 159.9 mm | 6.295 in

Depth 101 mm | 3.976 in

Ordering Tree



Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1

Environmental Specifications

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

COMMSCOPE®

NG4-CMDKORJ

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

