


MP-PP15M-12C-126



PIM Optimized Adjustable Monopole Platform with 15ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (12) 2-7/8in OD x 126in Antenna Pipes

Product Classification

Product Type	Co-location platform
Product Brand	PIM-guard

General Specifications

Mounting	Monopole, 304.8–1143 mm (12–45 in) OD
Pipe, quantity	12
Sectors, quantity	3

Dimensions

Height	3,200.4 mm 126 in
Face Width	4.572 m 15 ft
Width	4,572 mm 180 in
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Mounting Diameter, maximum	1,143 mm 45 in
Mounting Diameter, minimum	304.8 mm 12 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222
--------------------------------	-------------

MP-PP15M-12C-126

Packaging and Weights

Included	Plain end pipes (12) Platform Rail Ring mount
Packaging quantity	1
Weight, net	1,358.146 kg 2,994.2 lb