2160164-1 | L-002-DN-8F-M01WH/AY/D



Fiber indoor/outdoor drop cable, FTTH, 2 Fiber, Singlemode G.657.A1, Gel-free, meters jacket marking, White jacket color, Dca flame rating

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA North America
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	L-DN
General Specifications	
Cable Type	Drop Semi-tight buffer
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	White
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB SMF G657A MACL9/125 S LSZH EN50575 CLASS Dca [Serial NUMBER] [METRE MARK]
Subunit, quantity	1
Fibers per Subunit, quantity	1
Total Fiber Count	2
Dimensions	
Cable Length	2,000 m 6,561.68 ft
Buffer Tube/Subunit Diameter	0.9 mm 0.035 in
Diameter Over Jacket	4 mm 0.157 in

Representative Image

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2024



2160164-1 | L-002-DN-8F-M01WH/AY/D

Low Smoke Zero Halogen (LSZH)

ULSZH UV Stabilised Jacket Aramid Yarn Strength Elements GRP strength Member Buffered Fibres



Jacket Material

Mechanical Specifications

Minimum Bend Radius, unloaded 60 mm | 2.362 in Tensile Load, long term, maximum 600 N | 134.885 lbf Tensile Load, short term, maximum 1200 N | 269.771 lbf Compression 20 N/mm | 114.203 lb/in **Compression Test Method** IEC 60794-1 E3 Impact 5 N-m | 44.254 in lb Impact Test Method IEC 60794-1 E4 Strain Test Method IEC 60794-1 E1 Twist 5 cycles **Twist Test Method** IEC 60794-1 E7 **Optical Specifications** Fiber Type G.657.A1

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2024



2160164-1 | L-002-DN-8F-M01WH/AY/D

Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Cable Qualification Standards	IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	al
Environmental Space	Drop Ducted Façade Indoor/Outdoor UV resistant for outdoor and Low Smoke Zero Halogen
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5
Environmental Test Specifications	
Temperature Cycle	-30 °C to +60 °C (-22 °F to +140 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1

Packaging and Weights

20 kg/km | 13.439 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-8F-TB

Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2024

