## HCA-DO1G



Fiber Optic Drop Cable assembly, PRODIGY™ Connector core with Bayonet + full size converter included. 4.5 mm round cable

- Cable assembly with the Prodigy™ small form hardened connector
- Compact and small footprint, space-saving design for high-density environments
- Compatible with multiple hardened connectors

#### **Product Classification**

Regional Availability EMEA

**Product Type** Fiber drop cable assembly

Product Brand PRODIGY™

Product Series HCA

#### General Specifications

Cable TypeDielectric - Round

Connector A, quantity

Color, boot A Black

Color, connector A Black

Interface, Connector A Prodigy®

Interface, Connector B Unterminated

Jacket Color Black

Total Fibers, quantity 1


#### Dimensions

Cable Assembly Length Range (m) 3 - 609

Cable Outer Diameter4.5 mm (0.18 in)

### Ordering Tree





#### Mechanical Specifications

Minimum Bend Radius, loaded 75 mm | 2.953 in

Minimum Bend Radius, unloaded 25 mm | 0.984 in

**Tensile Load, long term, maximum** 300 N | 67.443 lbf

**Tensile Load, short term, maximum** 1200 N | 269.771 lbf

Cable Crush Resistance, maximum10 N/mm | 57.101 lb/in

**Dust Cap Pulling Force, minimum** 445 N | 100.04 lbf

Mating Durability, maximum 0.5 dB @ 100 cycles

#### **Optical Specifications**

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

**Insertion Loss, maximum, connector A** 0.4 dB

**Insertion Loss, typical** 0.15 dB

**Return Loss, minimum, connector A** 65 dB

COMMSC PE®

# HCA-D01G

## **Environmental Specifications**

**Installation temperature**  $0 \,^{\circ}\text{C}$  to +60  $^{\circ}\text{C}$  (-32  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Operating Temperature**  $-25 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-13 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Outdoor

Jacket UV Resistance UV stabilized

**Qualification Standards** IEC 61753-1

Packaging and Weights

Cable weight 30 kg/km | 20.159 lb/kft

