

# MTC3792U

---



Full Grating Monopole Co-location Platform Kit with Gates and Top Rail Kit, 10 in to 30 in OD, 12 ft 6 in face, includes twelve 2-3/8in OD x 96 in pipes

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Co-location platform
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Mounting</b>	Monopole, 254–762 mm (10–30 in) OD
<b>Pipe, quantity</b>	12
<b>Sectors, quantity</b>	3

## Dimensions

<b>Height</b>	2,438.4 mm   96 in
<b>Face Width</b>	3.81 m   12.5 ft
<b>Width</b>	3810 mm   150 in
<b>Pipe Length</b>	2,438.4 mm   96 in
<b>Mounting Diameter, maximum</b>	762 mm   30 in
<b>Mounting Diameter, minimum</b>	254 mm   10 in
<b>Pipe Outer Diameter</b>	60.96 mm   2.4 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact <a href="mailto:steelproducts@commscope.com">steelproducts@commscope.com</a> or call 800-255-1479
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Grating   Plain end pipes (12)   Platform   Rail   Ring mount
-----------------	---

# MTC3792U

---

**Packaging quantity** 1  
**Weight, net** 1,024.166 kg | 2,257.9 lb

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code