

# L4-CLAMP-3B

---



KwikClamp™ Hanger for 1/2 in coaxial cable, triple stack; includes hardware

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	KwikClamp™
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa   Minimum order quantity (MOQ) is 1 box

## General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	KwikClamp™ hanger
<b>Mounting</b>	3–25 mm angle iron   3–25 mm flat plate   Round Member 8-25 mm

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	170 mm   6.693 in
<b>Width</b>	32 mm   1.26 in
<b>Length</b>	42 mm   1.654 in
<b>Compatible Diameter, maximum</b>	17 mm   0.669 in
<b>Compatible Diameter, minimum</b>	15 mm   0.591 in
<b>Nominal Size</b>	1/2 in
<b>Hanger Spacing, maximum</b>	1.83 m   6.004 ft

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

# L4-CLAMP-3B

---

## Material Specifications

**Material Type** Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 48

**Weight, gross** 7.7 kg | 16.976 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power