

Fiber OSP cable, TeraSPEED® Single Jacket/Single Armor, Gel-Filled, 48 fibers, Outdoor Central Tube, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

O-CA

Portfolio CommScope®

Product Type Fiber OSP cable

General Specifications

Product Series

Armor Type Corrugated steel

Cable Type Central loose tube

Construction Type Armored

Subunit Type Gel-filled

Jacket Color Black

Jacket Marking Feet

Fibers per Subunit, quantity 12

Total Fiber Count 48


Dimensions

Buffer Tube/Subunit Diameter 6 mm | 0.236 in

Diameter Over Jacket 13 mm | 0.512 in

Representative Image





Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded195 mm | 7.677 inMinimum Bend Radius, unloaded130 mm | 5.118 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbfCompression44 N/mm | 251.246 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 464 m | 1,522.31 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2



Environmental Specifications

Installation temperature

-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | EN 187105

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze $-2 \,^{\circ}\text{C} \, \mid \, 28.4 \,^{\circ}\text{F}$

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 176 kg/km | 118.267 lb/kft

Regulatory Compliance/Certifications

Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Agency



Included Products

CS-8W-LT

 TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



TeraSPEED® G652D/G657A1 Singlemode Fiber

TeraSPEED®

Product Classification

Portfolio CommScope®

Product Type Optical fiber

General Specifications

Cladding Diameter 125 µm

 ${\bf Cladding\ Non-Circularity,\ maximum} \\ {\bf 0.7\ \%}$

Coating Diameter (Colored) 249 μm

Coating Diameter Tolerance (Colored) ±13 μm

Coating Diameter Tolerance (Uncolored) ±5 µm

 $\textbf{Coating/Cladding Concentricity Error, maximum} \hspace{1.5cm} 12~\mu m$

Core Diameter 8.3 μm

 $\textbf{Core/Clad Offset, maximum} \hspace{1.5cm} 0.5\,\mu\text{m}$

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

Macrobending, 20 mm Ø mandrel, 1 turn 0.75 dB @ 1,550 nm | 1.50 dB @ 1,625 nm

Macrobending, 30 mm Ø mandrel, 10 turns 0.25 dB @ 1,550 nm | 1.00 dB @ 1,625 nm

Macrobending, 60 mm Ø mandrel, 100 turns 0.05 dB @ 1,550 nm | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum 8.9 N | 2.001 lbf

COMMSCOPE®

CS-8W-LT

Coating Strip Force, minimum 1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

Attenuation, typical 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

Mode Field Diameter 10.4 μm @ 1,550 nm | 9.2 μm @ 1,310 nm | 9.6 μm @

1,385 nm

Mode Field Diameter Tolerance $\pm 0.4 \, \mu \text{m} \ @ \ 1310 \, \text{nm} \ | \ \pm 0.5 \, \mu \text{m} \ @ \ 1550 \, \text{nm} \ | \ \pm 0.6 \, \mu \text{m}$

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sgrt(km)

Standards Compliance IEC 60793-2-10, edition 6, model A1a.4 | ITU-T G.652.

D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

COMMSCOPE®

CS-8W-LT

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

