



ReadyPATCH® ULL Multimode OM5 MPO-12 Distribution Module, 6 duplex LC non-keyed aqua adapters to 1X12f MPO/UPC non-pinned, Method B Enhanced

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	ReadyPATCH®

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	1
Color, front	Aqua
Color, rear	Gray
Data Module Type	Standard
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	12
Total Ports, quantity, front	6

Dimensions

Height	27.94 mm 1.1 in
Width	129.54 mm 5.1 in
Depth	127 mm 5 in

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Fiber Type OM5, LazrSPEED® wideband
Insertion Loss, maximum 0.35 dB

Environmental Specifications

Safety Standard c-UL-us

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

