

RT-DF15-4-120



PIM-Guard High Capacity DUAL Non-Penetrating Roof Frame with Optimized Antenna Spacing 15 ft face, four 2-7/8 in OD x 120 in pipes

Product Classification

Product Type	Non-penetrating roof frame
Product Brand	PIM-guard

General Specifications

Mounting	Non-penetrating
Pipe, quantity	4

Dimensions

Height	3,048 mm 120 in
Face Width	4.572 m 15 ft
Width	4,572 mm 180 in
Length	2.377 m 7.8 ft
Pipe Length	3,048 mm 120 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

RT-DF15-4-120

Included	Ballast tray Frame Plain end pipes (4)
Packaging quantity	1
Weight, net	866 kg 1,909.201 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	------------------------------------------------